


## General Information

- Designed for rugged field use by the surveyor, engineer or contractor
- More accurate than tolerances established by the National Bureau of Standards when fully supported with standard tension of 4.5lbs.
- Tape stretches 0.0011”/ foot per additional pound of tension over 4.5lbs.
- Durable, waterproof and able to withstand breakage and abrasion under extreme conditions
- Non-conductive construction material allows safe use around electrical hazards

## Pro Series Fiberglass Tapes

- 60 strand fiberglass encased in two layers of PVC for extra durability
- Two color, two sided blade includes fractional and decimal graduations
- 3:1 rewind
- Dual material grip on handle and side of cross bars, for added comfort
- Rotating mouthpiece, reduces strain on the blade, and maintains blade alignment as it extends and retracts
- Includes 3 interchangeable end attachments, snap fit lock mechanism, for quick changes in the field
  - Standard folding, two position end hook for inside and outside readings
  - appraiser's hook, grips on large items such as downspouts and concrete (for estimation)
  - ring attachment, fits on stake (included) for one person measurements
- Integrated storage in handle, with sliding latch closure, to hold all 3 end attachments



Cat. No.	UPC No.	Blade Size		Blade Style	Pack Wt.		Case Pack
		Width	Length		lb	kg	
PSFE100	037103224811	3/4"	100'	C11	6.6	3.0	2
PSFE200	037103224828	3/4"	200'	C11	9.3	4.2	2
PSFE300	037103224804	3/4"	300'	C11	11.3	5.1	2
PSFM030CME	037103233981	3/4"	30m/100'	C12	6.6	3.0	2
PSFM060CME	037103233998	3/4"	60m/200'	C12	9.3	4.2	2
PSFM100CME	037103234001	3/4"	100m /328'	C12	14.5	6.6	2



### Replacement end attachment Kit

Includes all 3 end attachments

Cat. No.	UPC No.	Pack Wt.		Shelf Pack
		lb	kg	
PSFE3PCKIT	037103231635	0.2	0.1	3