

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 405TTFS7297
Catalog No: Y391
75,1785/890,TEFC,405T,3/60/60/460#460
Other Purpose



Regal and Marathon are trademarks of Regal Beloit Corporation or one of its affiliated companies.
©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E

REGAL




Nameplate Specifications

Output HP	75,18.75 Hp	Output KW	56 kW
Frequency	60 Hz	Voltage	460 V
Current	83,27 A	Speed	1785,890 rpm
Service Factor	1.15	Phase	3
Efficiency	94.1 %	Duty	CONTINUOUS
Insulation Class	F	Design Code	1VT
KVA Code	H	Frame	405T
Enclosure	TEFC	Overload Protector	NOT
Ambient Temperature	40 °C	Drive End Bearing Size	6316
Opp Drive End Bearing Size	6313	UL	Recognized
CSA	Y	CE	Y
IP Code	55		

Technical Specifications


Electrical Type	SQ CAGE IND RUN	Starting Method	ACROSS THE LINE
Poles	4/8	Rotation	REV
Mounting	RIGID	Motor Orientation	HORIZONTAL
Drive End Bearing	BALL	Opp Drive End Bearing	BALL
Frame Material	CAST IRON	Shaft Type	T
Overall Length	37.14 in	Frame Length	16.75 in
Shaft Diameter	2.88 in	Shaft Extension	7.5 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	B-SS508859-1675	Connection Diagram	A-EE7322




A- EE7322

FOR DUAL LEADS


LOW SPEED



HIGH SPEED



THREE PHASE MOTOR
SINGLE VOLTAGE
TWO SPEED - SGL. WDG.
VARIABLE TORQUE




VIEW OF TERMINAL END


T612C

T48B

LOW SPEED



HIGH SPEED



				✓ MAX. SURFACE ROUGHNESS UNLESS NOTED OTHERWISE	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL. ON XX± XXX± .005 XXXX± .0005 ANGLES±					
				MATL SPEC				DRAWN BY PGK	12-26-1996	
								CHKD BY ML	01-07-1997	
				FINISH						
7	01-08-1997	REDRAWN ON CADD		PGK	REFERENCE DRW.	WAUSAU, WISCONSIN 54401			APPD BY TB	01-07-1997

SHOP BOOK

PURCHASED

DISTRIBUTION - WA - LB - WP - LM - BR

CADD FILE NO.

EE7322

CERTIFICATION DATA SHEET

Model#: 405TTFS7297 AP **WINDING#:** T405(4-8)11 NONE 1
CONN. DIAGRAM: A-EE7322 **ASSEMBLY:** F1/F2 CAPABLE
OUTLINE: B-SS508859-1675

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
75&18 3/4	56&14	900	1785&890	405T	TEFC	H	1VT

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/60	460	83&27	ACROSS THE LINE	CONTINUOUS	F1	1.15/1.15	40	3300

FULL LOAD EFF: 94.1&92.4	3/4 LOAD EFF: 92.4	1/2 LOAD EFF: 91	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 90&71.5	3/4 LOAD PF: 67	1/2 LOAD PF: 57	90.9	SQ CAGE IND RUN	12.5

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
112 LB-FT	118	123 LB-FT 110	222 LB-FT 198	80

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
55 dBA	65 dBA	27 LB-FT^2	- LB-FT^2	- SEC.	-	1400 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	PREMIUM SEVERE DUTY	NONE	FALSE	NONE	BLUE (EPOXY)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL	BALL						
6316	6313	POLYREX EM	T	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

*
N
O
T
E
S
*

INVERTER TORQUE: NONE		
INV. HP SPEED RANGE: NONE		
ENCODER: NONE		
NONE	NONE	
NONE	NONE	PPR
BRAKE: NONE NONE		
NONE	P/N	NONE
NONE	NONE	
- FT-LB	NONE V	NONE Hz

DATE: 06/22/2017 01:04:47 AM
 FORM 3531 REV.3 02/07/99
 ** Subject to change without notice.