


# Martin Sprocket Nomenclature

Sprocket Nomenclature



# of Strands

- Blank Single
- D** Double
- E** Triple
- F** Quadruple
- DS** Double Single

**D 160 B 16 H 2 1/4**

Bore Size

**Special Instructions**

- H** Hardened Teeth
- SS** Stainless Steel

# of Teeth


Chain Pitch (measured in eighths)

- 25 = 2/8 = 1/4"    100 = 10/8 = 1 1/4"
- 35 = 3/8 = 3/8"    120 = 12/8 = 1 1/2"
- 40 = 4/8 = 1/2"    140 = 14/8 = 1 3/4"
- 41 = 4/8 = 1/2"    160 = 16/8 = 2"
- 50 = 5/8 = 5/8"    180 = 18/8 = 2 1/4"
- 60 = 6/8 = 3/4"    200 = 20/8 = 2 1/2"
- 80 = 8/8 = 1"      240 = 24/8 = 3"

Sprocket Type

- A** Plate Only
- B** Hub One Side
- C** Hub Both Sides
- D** Detachable Hubs
- JA, SH,...** QD
- BTB** Taper Bushed
- H, P, Q,...** MST®
- BS** Bored-To-Size

## Types of Sprockets



[www.martinsprocket.com](http://www.martinsprocket.com) - 817 258 3000

Copyright© 2017 Martin Sprocket & Gear, Inc. • All Rights Reserved • CARD-SPK 1/25/2017