



Speeds & Feeds

Product Table: End Mills for Aluminum Alloys - Square - 2 & 3 Flute

Characteristics: 2x, 3x Length of Cut, 2 & 3 Flutes

Series: ARM-XXX-X, ARM-XXXX-X, ARMM-XXX-X

Cutter Series	MATERIAL	SFM	Chip Load (IPT) By Cutter Diameter												Depth of Cut		
			0.015	0.031	0.047	0.062	0.078	0.093	0.125	0.187	0.250	0.312	0.375	0.500	Radial	Axial	
Uncoated	ALUMINUM ALLOYS																
	Casting (2xx, 5xx, 7xx, 8xx)	750	Slotting	.00020	.00041	.00062	.00082	.00103	.00123	.00165	.00247	.00330	.00432	.00520	.00693	1x Dia	.5x Dia
	Wrought (1xxx, 2xxx, 3xxx, 5xxx, 6xxx, 7xxx, 8xxx)	1000	Roughing	.00023	.00048	.00072	.00095	.00120	.00143	.00193	.00288	.00385	.00505	.00606	.00809	.5x Dia	.5x - 1x Dia
	MAGNESIUM ALLOYS	1500	Finishing	.00025	.00051	.00078	.00102	.00129	.00153	.00206	.00309	.00413	.00541	.00650	.00866	.1x Dia	.5x - 1x Dia
	ZINC ALLOYS	800	Max	.00026	.00055	.00083	.00109	.00137	.00164	.00220	.00329	.00440	.00577	.00693	.00924	-	-
	COPPER ALLOYS																
	High Coppers - 90%+ (C1xxxx)	225	Slotting	.00016	.00033	.00050	.00065	.00082	.00098	.00132	.00197	.00264	.00346	.00416	.00554	1x Dia	.5x Dia
	Brass (Copper Zinc alloys, C2xxxx, C3xxxx, C4xxxx, C66400-C69800)	500															
	Phosphor Bronzes (Copper Tin alloys, C5xxxx)	225	Roughing	.00018	.00038	.00058	.00076	.00096	.00115	.00154	.00230	.00308	.00404	.00485	.00647	.5x Dia	.5x - 1x Dia
	Aluminum Bronzes (Copper Aluminum alloys, C60600-C64200)	500															
	Silicon Bronzes (Copper Silicon alloys, C64700-C66100)	500	Finishing	.00020	.00041	.00062	.00082	.00103	.00123	.00165	.00247	.00330	.00432	.00520	.00693	.1x Dia	.5x - 1x Dia
	Copper Nickels, Nickel Silvers (Copper Nickel alloys, C7xxxx)	225															
	Cast Copper Alloys (C83300-C86200, C86400-C87900, C92200-C95800, C97300-C97800, C99400-C99700)	550	Max	.00021	.00044	.00066	.00087	.00110	.00131	.00176	.00263	.00352	.00461	.00554	.00739	-	-
TiB2	ALUMINUM ALLOYS																
	Casting (2xx, 5xx, 7xx, 8xx)	1000	Slotting	.00026	.00053	.00081	.00106	.00134	.00160	.00215	.00321	.00429	.00562	.00676	.00901	1x Dia	.5x Dia
	Wrought (1xxx, 2xxx, 3xxx, 5xxx, 6xxx, 7xxx, 8xxx)	1400	Roughing	.00030	.00062	.00094	.00124	.00156	.00186	.00250	.00374	.00501	.00656	.00788	.01051	.5x Dia	.5x - 1x Dia
	MAGNESIUM ALLOYS	2000	Finishing	.00032	.00066	.00101	.00133	.00167	.00199	.00268	.00401	.00536	.00703	.00845	.01126	.1x Dia	.5x - 1x Dia
	ZINC ALLOYS	1100	Max	.00034	.00071	.00108	.00142	.00178	.00213	.00286	.00428	.00572	.00750	.00901	.01201		
Amorphous Diamond	ALUMINUM (High Silicon)																
	Casting - 3%-5% Si (3xx, A3xx, C3xx, 4xx, A4xx, B4xx)	2500	Slotting	.00022	.00045	.00068	.00090	.00113	.00135	.00182	.00272	.00363	.00476	.00572	.00762	1x Dia	.4x Dia
	Casting - 5%-8% Si (3xx, A3xx, C3xx, 4xx, A4xx, B4xx)	2000															
	Casting - 8%-12% Si (3xx, A3xx, C3xx, 4xx, A4xx, B4xx)	1500	Roughing	.00025	.00053	.00080	.00105	.00132	.00158	.00212	.00317	.00424	.00555	.00667	.00889	.4x Dia	.3x - .8x Dia
	Casting - 12%-16% Si (3xx, A3xx, C3xx, 4xx, A4xx, B4xx)	1000	Finishing	.00027	.00056	.00085	.00113	.00142	.00169	.00227	.00339	.00454	.00595	.00715	.00953	.1x Dia	.5x - 1x Dia
	Wrought - 5%-8% Si (4xxx)	2200															
	Wrought - 8%-12% Si (4xxx)	1700	Max	.00029	.00060	.00091	.00120	.00151	.00180	.00242	.00362	.00484	.00634	.00762	.01016	-	-
	COPPER ALLOYS																
	High Coppers - 90%+ (C1xxxx)	800	Slotting	.00017	.00036	.00055	.00072	.00091	.00108	.00145	.00217	.00290	.00381	.00457	.00610	1x Dia	.4x Dia
	Brass (Copper Zinc alloys, C2xxxx, C3xxxx, C4xxxx, C66400-C69800)	1500															
	Phosphor Bronzes (Copper Tin alloys, C5xxxx)	800															
	Aluminum Bronzes (Copper Aluminum alloys, C60600-C64200)	1000	Roughing	.00020	.00042	.00064	.00084	.00106	.00126	.00169	.00253	.00339	.00444	.00534	.00711	.4x Dia	.3x - .8x Dia
	Silicon Bronzes (Copper Silicon alloys, C64700-C66100)	1000															
	Copper Nickels, Nickel Silvers (Copper Nickel alloys, C7xxxx)	800	Finishing	.00022	.00045	.00068	.00090	.00113	.00135	.00182	.00272	.00363	.00476	.00572	.00762	.1x Dia	.5x - 1x Dia
	Cast Copper Alloys (C80100-C82800, C86300, C90200-C91700, C96200-C96600, C99300)	150															
	Cast Copper Alloys (C83300-C86200, C86400-C87900, C92200-C95800, C97300-C97800, C99400-C99700)	750	Max	.00023	.00048	.00073	.00096	.00121	.00144	.00194	.00290	.00387	.00507	.00610	.00813	-	-

Please note:

All posted speed and feed parameters are suggested starting values that may be increased given optimal setup conditions. If less than minimum Axial or Radial DOC values are used, increased feed rates are possible. If greater than maximum Axial or Radial DOC values are used, decreased feed rates may be needed.

If you require additional information, Micro100 has a team of technical experts available to assist you through even the most challenging applications. Please contact us at **800-421-8065** or micro100tech@harveypformance.com.

WARNING: Cutting tools may shatter under improper use. Government regulations require use of safety glasses and other appropriate safety equipment in the vicinity of use.