

Drain Cocks DCE and DCEO Series

Applications: Compressor Receivers, Radiators and Pool Equipment Where Stem Removal is Not a Requirement

- Construction: Brass Body and Stem with Zinc Plated Steel Handle
- Metal to Metal Seat (DCE Series)
- Viton O-Ring (DCEO)
- Maximum Pressure 200 PSI
- Maximum Temperature -25 °F to 250 °F
- Thread Sealant (DCE Series)



DCE	DCEO
NPT	Part No.
1/8"	DCE-18
1/4"	DCE-25
1/4"	DCEO-25
3/8"	DCE-38
1/2"	DCE-50

DT Drain Cock Series

Applications: Designed for Applications Where the Traditional Drain Cock is Easily Damaged

- Construction: Brass Body and Knurled Brass Stem
- Opens Easily and Closes with Minimum Effort
- Nitrile O-Ring Ensures a Bubble Tight Seal
- Maximum Pressure: 200 PSI
- Maximum Temperature: 250 °F
- Thread Sealant



NPT	Part No.
1/4"	DT25

Drain Cock with Pull Cord DP & DM Series

Applications: Industrial and Automotive

- Construction: Brass Body, Washer and Stem, Stainless Steel Spring and Nitrile O-Ring
- Maximum Pressure: 200 PSI
- Maximum Temperature: 200 °F
- Thread Sealant (DP)




DP	DM
Cable Length	Part No.
60"	DP25
36"	DM25

Stem tilts to open the valve with minimum pull cord force, spring returns the stem to positively seal against the O-ring when force on the cord is released

Carry Tank Manifold with Integral Safety Valve

- Construction: Brass Body, Stainless Steel Spring, Nitrile O-Rings and Silicone Rubber Safety Valve Seals
- Design Incorporates a Tank Filler Valve into the Built-In Shut-Off Valve
- Mates to a Typical Tire Chuck for Easy Tank Pressurization
- Non-Code Safety Valve is Factory Preset at 150 PSI
- Includes Tank Pressure Gauge Port



Inlet Male	Outlet Female	Gauge Port	Part No.
1/2"	1/4"	1/4"	CTM-150

Filler Valve

Applications: Use Wherever a Method of Inflating a Tank with a Standard Air Chuck is Required

- Construction: Nickel Plated Body, Brass Valve Core with Viton® and Teflon ®Seals
- Black Plastic Cap
- Maximum Temperature: 250 °F
- Maximum Pressure: 250 PSI




NPT	Part No.
1/8"	TV18NP


KEY NO.	DESCRIPTION
1.	SPRING
2.	O-RING
3.	CAP
4.	STEM
5.	SLEEVE
6.	CABLE
7.	BODY
8.	STEM CUP

** KEY CHARACTERISTICS **
1. LEAKAGE -- MUST NOT EXCEED 20 SCCM AT 135 PSI

THIS DOCUMENT CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION OF CONTROL DEVICES INC. AND MUST BE USED STRICTLY IN ACCORDANCE WITH THE LIMITED PURPOSE FOR WHICH IT WAS SUBMITTED. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DOCUMENT IS EXPRESSLY PROHIBITED, EXCEPT AS OTHERWISE AGREED IN WRITING.

DATE	SYM	REVISION RECORD	ECN NO.	CK.
1/8/01	A	RELEASE TO PRODUCTION	01-004	
1/28/05	B	DATE CODE WAS "M""Y", STEM WAS ONE PIECE	05-063	



TOLERANCES (EXCEPT AS NOTED)		 control devices inc. 711 HANLEY INDUSTRIAL COURT ST. LOUIS, MISSOURI 63144				
DECIMAL ± .005	SEE NOTE 1	MATERIAL	SCALE 1X	SIZE B	DRAWN BY JVH	
FRACTIONAL ± .015					APPROVED BY	
ANGULAR ± 2°						
DATE 10/31/00	TITLE HEAVY DUTY CABLE OPERATED DRAIN VALVE, ASSEMBLY					
		CAD FILE	DRAWING NUMBER			
		Q:\ENGR\PARTDWGS\A-G037.DWG	DM25-0A036REV B			

ALL DIMENSIONS ARE IN INCHES.