


Back Mount Flanged Liquid Filled Pressure Gauge



The liquid filled gauge dampens the effect of pulsation and vibration, while also perpetually lubricating the movement and keeping contaminants such as dirt away from all moving parts which will extend the life of the gauge. Typically used on hydraulic and pneumatic systems as well as any commercial or industrial applications not corrosive to brass or bronze wetted parts where silicone filling is suitable for use.

Built-In Snubber
304 Stainless Steel Case and Bezel
Copper Alloy Wetted Parts
Polycarbonate Lens
Liquid Filled: Silicone
Accuracy 3-2-3% of Span ASME B40.1 Grade B (1-1/2" & 2" Dials)
Accuracy 2-1-2% of Span ASME B40.1 Grade A (2-1/2" & 4" Dials)
Dual Scale: PSI/Bar (x 100=kPa)
Ambient Temperature: -40 F to 140 F
Individually Boxed
Design Meets or Exceeds ASME B40.100 Pressure Gauge Standard

Part No.	Dial Size	Connection	A (In)	B (In)	C (In)	D (In)	E (In)	F (In)	Wt. (lbs.)
LSCB25-160F	2.5"	1/4"	2.68	1.14	0.94	2.08	2.4	3.46	0.37

"WARNING" - Misuse of product may cause an explosion and personal injury. Read ANSI - B40.1 and apparatus installation operating instructions before using.
DO NOT USE ON OXYGEN SERVICE
MADE IN CHINA



WARNING: This product can expose you to chemicals, including lead, which is known to the State of California to cause cancer and reproductive harm. For more information go to www.P65Warnings.CA.gov

Drawing Date: 8/2023
Rev Level-Date: R1 8/2023