



U - Clamp Dry Gauges

- A Durable Dry Utility Gauge Designed to Look Good From the Front or Back of the Panel
- Suitable for Air, Water, Oil or Any Other Media Not Corrosive to Brass
- Other Connection Locations, Mounting Styles and Accessories Available

Specifications:

Dial Sizes: 1-1/2", 2" and 2-1/2"
Connection Sizes: 1/8" NPT on 1-1/2"
1/4" NPT on 2" and 2-1/2" Dials


- ASME B40.100 Compliant
- Chrome Plated Steel Case & Bezel
- Copper Alloy Wetted Parts
- Plastic Lens
- Accuracy 3-2-3 % of Span ASME B40.1 Grade B
- Ambient Temperature: -50 ° F to 160 ° F
- Dual Scale: PSI/Bar (X 100= kPa) Standard

Vacuum Gauges

Range	Major Increments	Minor Increments
30/0"VAC	5" hg	.5" hg

Pressure Gauges

Range	Major Increments	Minor Increments
0/15	2 psi	.1 psi
0/30	5 psi	.5 psi
0/60	10 psi	1 psi
0/100	20 psi	2 psi
0/160	20 psi	2 psi
0/200	40 psi	5 psi
0/300	50 psi	5 psi
0/400	50 psi	5 psi
0/600	100 psi	10 psi
0/3000	500 psi	50 psi



Dial Size	Pressure Gauges	Vacuum Gauges	A	B	C	D	G	E
1-1/2"	PSB15-PSI-U	VSB15-030U	1.84"	1.03"	.63"	1.61"	1.61"	1/8"
2"	PSB20-PSI-U	VSB20-030U	2.31"	1.18"	.73"	1.84"	2.04"	1/4"
2-1/2"	PSB25-PSI-U	VSB25-030U	2.68"	1.12"	.76"	1.87"	2.44"	1/4"

Dial Size	Available PSI
1-1/2"	15, 30, 60, 100, 160, 200, and 300
2"	Same As Above Plus 400
2-1/2"	15, 30, 60, 100, 160, 200, 300, 400, 600 and 3000