


Dial Gauge Micrometer

Item number: 107-204

Images



Description

This Dial Gauge Micrometer allows you to quickly measure mass-produced parts. It offers the following benefits:

- Designed to mount a dial or a Digital indicator for direct GO/NG judgement of mass-produced parts.
- You can take rapid measurements thanks to its anvil retracting trigger.
- 3 mm anvil retracting stroke.

Features

Inch-Metric:	Metric
Range:	75 - 100 mm
Graduation:	0.01 mm
Delivered:	Including box, with spanner, setting standard
Anvil retracting stroke:	3 mm
Spindle feed error:	3 μ m
Flatness:	0,6 μ m
Parallelism:	3 μ m
Measuring face:	Carbide-tipped, micro-lap finish
Measuring spindle:	With spindle lock, \varnothing 6,35 mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish \varnothing 18 mm
Measuring force:	5 - 10 N
Mass:	630 g

Optional accessories:



Digital Indicator ID-C

12,7mm, 0,001mm, Flat Back
Art No. 543-390B
Suggested retail price: 344.00 €*

Promotion!



Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm
Art No. 2046AB
Promo price: 38.00 €*
Suggested retail price: 48.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: 56.00 €*
Suggested retail price: 70.00 €*



Digital Indicator ID-C

12,7mm, 0,01mm, Flat Back
Art No. 543-400B
Suggested retail price: 259.00 €*

Promotion!



Dial Gauge, Flat Back, ISO Type

Jewelled Bearing, Shockproof, 1mm, 0,001mm

Art No. 2109AB-10

Promo price: **84.00 €***

Suggested retail price: ~~106.00 €*~~

Standard accessories:



Micrometer Setting Standard

Length: 75mm

Art No. 167-103

Suggested retail price: **37.00 €***