

Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 1045A-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	5 mm
Range per rev.:	1 mm
Dial reading:	0-50-0
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,01 mm
MPE first one revolution:	$\pm 10 \mu\text{m}$
MPE first 2 1/2 revolutions:	$\pm 10 \mu\text{m}$
MPE > 2 1/2-10 revolutions:	$\pm 13 \mu\text{m}$
H MPE (Hysteresis):	$3 \mu\text{m}$
R MPE (Repeatability):	$\pm 3 \mu\text{m}$
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator
Art No. 21AAB363
Price on application



Spindle Lifting Lever

for S-Type and A-Type Serie 1
Art No. 902100
Price on application



Spindle Lifting Cable

for Indicator, L=500mm
Art No. 21JZA295
Price on application



**Spindle Lifting Cable with
Auto Stop**

for Indicator, L=300mm
Art No. 21JZA301
Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*