

# Micrometer Head, Differential Screw

Item number: 110-102

## Images



## Description

An ultra-high resolution, non-digital Mitutoyo micrometer head with M12 clamp-nut stem and heavy-duty  $\lambda \div 8$ mm non-rotating spindle fitted with flat tungsten-carbide tip.

## Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	0 - 2.5 mm
<b>Graduation:</b>	0,0001 mm
<b>Maximum Permissible Error J MPE (Narrow):</b>	$\pm 1,5 \mu\text{m}$
<b>Max. Permissible Error J MPE:</b>	$\pm 5 \mu\text{m} / \pm 1,5 \mu\text{m}$
<b>Spindle end:</b>	Flat
<b>Stem <math>\varnothing</math>:</b>	12 mm
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	9.5 mm
<b>Special features:</b>	Fine Graduation
<b>Delivered:</b>	In a paper box with spanner 200154
<b>Measuring face:</b>	Carbide tipped
<b>Mass:</b>	150 g

## Dimensions

