





Outside Microm. Anvil Extension Collar

Item number: 105-431

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.


It offers you the following benefits:

- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50 mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Measuring spindle:	With spindle lock, ø8 mm, spindle pitch 0,5 mm
Range:	52 - 56 "
Scale:	Thimble and sleeve satin chrome finish, ø21 mm
Graduation:	0,001"
Limit of error:	±0,00125"
Delivered:	Including box, with spanner, setting standard (2 pcs.), 2" extension collar
Spindle feed error:	0.0003 inch
Flatness:	0,000052"
Parallelism:	0.00063"
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5-10 N
Extension collar:	2"
Remarks:	With workpiece stop 100 mm adjustable
Mass:	11.9 kg

Dimensions



L: 1425 mm

a: 700 mm


Accessories

Standard accessories:

Micrometer Setting Standard

Length: 52"

Art No. 167-416

Suggested retail price: 737.00 €*


Micrometer Setting Standard

Length: 54"

Art No. 167-418

Suggested retail price: 763.00 €*