


# Micrometer Head, Differential Screw

Item number: 110-105-10

## Images



## Description

This is a differential screw translator (extra-fine feed) type of micrometer head. It offers you the following benefits:

- Micrometer head with ultra-fine rate of travel.
- With its non-rotating spindle it is particularly suited to fine adjustments.
- The differential travel mechanism with double spindle enables ultra-sensitive travel

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box with spanner 200154
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	0 - 1 mm
<b>Graduation:</b>	0.001 mm
<b>Maximum Permissible Error J MPE (Narrow):</b>	$\pm 1.5 \mu\text{m}$
<b>Max. Permissible Error J MPE:</b>	$\pm 3 \mu\text{m} / \pm 1.5 \mu\text{m}$
<b>Spindle end:</b>	Flat
<b>Stem <math>\varnothing</math>:</b>	12 mm
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	9.5 mm
<b>Measuring face:</b>	Carbide tipped (>90 HRA)
<b>Mass:</b>	150 g

## Dimensions

