

## Point Micrometer with Carbide

### Tip

Item number: 112-166

#### Images




#### Description

A Mitutoyo non-digital micrometer provided with pointed spindle and anvil to enable measurement within curved, slotted features, such as drilling-bit web thicknesses. A ratchet stop guarantees repeatable measurement.


#### Features

|                                      |  |
|--------------------------------------|--|
| <b>Digital/Analog:</b>               | Analog   |
| <b>Inch-Metric:</b>                  | Metric   |
| <b>Range:</b>                        | 25 - 50 mm   |
| <b>Graduation:</b>                   | 0,01 mm  |
| <b>Max. Permissible Error J MPE:</b> | $\pm 3 \mu\text{m}$  |
| <b>Delivered:</b>                    | Including box, spanner, setting standard   |
| <b>Measuring face:</b>               | Carbide pointed or hardened steel spindle and anvil, measuring point radius 0.3 mm |
| <b>Tip:</b>                          | 15°  |
| <b>Measuring spindle:</b>            | With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,5 mm                     |
| <b>Scale:</b>                        | Thimble and sleeve satin chrome finish, $\varnothing 18$ mm                        |
| <b>Measuring force:</b>              | 3 - 8 N  |
| <b>Mass:</b>                         | 305 g  |

#### Dimensions



- L:** 80.3 mm
- a:** 12.8 mm
- b:** 12 mm
- c:** 49 mm



- L:** 80.3 mm
- a:** 12.8 mm
- b:** 12 mm
- c:** 49 mm

**Accessories**

Optional accessories:



**Micrometer Stand, 45° Angle Type**

for Micrometer 0-50mm/0-2"  
 Art No. 156-105-10  
 Suggested retail price: 58.00 €\*



**Micrometer Stand, Adjustable Angle Type**

for Micrometer 0-100mm/0-4"  
 Art No. 156-101-10  
 Promo price: **56.00 €\***   
 Suggested retail price: ~~70.00 €\*~~

Standard accessories:



**Micrometer Setting Standard**

Length: 25mm  
 Art No. 167-101  
 Suggested retail price: 33.00 €\*

