

Micrometer Head, Differential Screw

Item number: 110-115-10

Images



Description

This is a differential screw translator (extra-fine feed) type of micrometer head. It offers you the following benefits:

- Micrometer head with ultra-fine rate of travel.
- With its non-rotating spindle it is particularly suited to fine adjustments.
- The differential travel mechanism with double spindle enables ultra-sensitive travel

Features

| | |
|--|------------------------------------|
| Digital/Analog: | Analog |
| Delivered: | In a paper box with spanner 200154 |
| Inch-Metric: | Inch |
| Range: | 0 - 0,02 " |
| Graduation: | 0.00002" |
| Maximum Permissible Error J MPE (Narrow): | $\pm 0,00006$ " |
| Max. Permissible Error J MPE: | ± 0.00015 " / ± 0.00006 " |
| Spindle end: | Flat |
| Stem \varnothing: | 0.5" |
| Stem: | w/ clamp nut |
| Fixture thickness for clamp nut: | 9.5 mm |
| Measuring face: | Carbide tipped (>90 HRA) |
| Mass: | 150 g |