

Micrometer Head, Differential Screw

Item number: 110-117-10

Images



Description

This is a differential screw translator (extra-fine feed) type of micrometer head. It offers you the following benefits:

- Micrometer head with ultra-fine rate of travel.
- With its non-rotating spindle it is particularly suited to fine adjustments.
- The differential travel mechanism with double spindle enables ultra-sensitive travel

Features

Digital/Analog:	Analog
Delivered:	In a paper box with spanner 200154
Inch-Metric:	Inch
Range:	0-0,02 "
Graduation:	0.00002"
Maximum Permissible Error J MPE (Narrow):	$\pm 0,00006$ "
Max. Permissible Error J MPE:	± 0.00015 " / ± 0.00006 "
Spindle end:	Spherical (SR10)
Stem \varnothing:	0.5"
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	9.5 mm
Measuring face:	Carbide tipped (>90 HRA)
Mass:	150 g