

Point Micrometer with Carbide Tip

Tip

Item number: 112-237

Images




Description

A Mitutoyo non-digital micrometer provided with pointed spindle and anvil to enable measurement within curved, slotted features, such as drilling-bit web thicknesses. A ratchet stop guarantees repeatable measurement.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.00015"
Delivered:	Including box, spanner
Measuring face:	Carbide pointed or hardened steel spindle and anvil, measuring point radius 0.3 mm
Tip:	30°
Measuring spindle:	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
Measuring force:	3 - 8 N
Mass:	205 g

Dimensions




L: 55.3 mm

a: 12.8 mm

b: 10 mm

c: 38 mm



L: 55.3 mm

a: 12.8 mm

b: 10 mm

c: 38 mm

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"

Art No. 156-105-10

Suggested retail price: 58.00 €*



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: 56.00 €*

Suggested retail price: 70.00 €*