


# Micrometer Head, Differential Screw

Item number: 110-504-10

## Images



## Description

This is a differential screw translator (extra-fine feed) type of micrometer head. It offers you the following benefits:

- Micrometer head with ultra-fine rate of travel.
- With its non-rotating spindle it is particularly suited to fine adjustments.
- The differential travel mechanism with double spindle enables ultra-sensitive travel

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box with spanner 200154
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0 - 0,02 "
<b>Graduation:</b>	A: 0.001" / B: 0.00002"
<b>Maximum Permissible Error J MPE (Narrow):</b>	$\pm 0,00006$ "
<b>Max. Permissible Error J MPE:</b>	$\pm 0.00015$ " / $\pm 0.00006$ "
<b>Spindle end:</b>	Spherical (SR3)
<b>Stem <math>\varnothing</math>:</b>	375"
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	11.5 mm
<b>Special features:</b>	Range A: 0 - 0.5", Range B: 0-0.006"
<b>Measuring face:</b>	Hardened steel (> 60 HRC)
<b>Mass:</b>	110 g