

Point Micrometer with Carbide

Tip

Item number: 112-238

Images



Description

A Mitutoyo non-digital micrometer provided with pointed spindle and anvil to enable measurement within curved, slotted features, such as drilling-bit web thicknesses. A ratchet stop guarantees repeatable measurement.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	1 - 2 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.00015"
Delivered:	Including box, spanner, setting standard
Measuring face:	Carbide pointed or hardened steel spindle and anvil, measuring point radius 0.3 mm
Tip:	30°
Measuring spindle:	With spindle lock, ø6,35 mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	3 - 8 N
Mass:	305 g

Dimensions



Micrometer Setting Standard

Length: 1"

Art No. 167-141

Suggested retail price: 33.00 €*
