

## Point Micrometer with Carbide Tip

### Tip

Item number: 112-167

#### Images




#### Description

A non-digital Mitutoyo micrometer provided with pointed spindle and anvil to enable measurement within curved, slotted features, such as drilling-bit web thicknesses. A ratchet stop guarantees repeatable measurement.

#### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	50 - 75 mm
<b>Graduation:</b>	0,01 mm
<b>Max. Permissible Error J MPE:</b>	$\pm 3 \mu\text{m}$
<b>Delivered:</b>	Including box, spanner, setting standard
<b>Measuring face:</b>	Carbide pointed or hardened steel spindle and anvil, measuring point radius 0.3 mm
<b>Tip:</b>	15°
<b>Measuring spindle:</b>	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
<b>Measuring force:</b>	3 - 8 N
<b>Mass:</b>	370 g

#### Dimensions




L: 105.3 mm

a: 12.8 mm

b: 14 mm

c: 60 mm



L: 105.3 mm

a: 12.8 mm

b: 14 mm

c: 60 mm

## Accessories

Optional accessories:

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10

**Promo price: 56.00 €\***   
~~Suggested retail price: 70.00 €\*~~

Standard accessories:



### Micrometer Setting Standard

Length: 50mm

Art No. 167-102

Suggested retail price: 36.00 €\*