


3 Flute V-Anvil Micrometer

Item number: 114-204

Images



Description

This V-Anvil Micrometer helps you measure cutting tools and taps.


It offers the following benefits:

- It measures the outside diameter of cutting tools (such as taps, reamers, end mills) which have three or five flutes.
- V-anvils with a centreline groove are available for measuring the pitch diameter of taps by the single-wire method.


Features

Digital/Analog:	Analog
Delivered:	Including box, spanner, setting standard
Inch-Metric:	Metric
Range:	2.3 - 25 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	±4 µm
Anvil:	Without groove
Measuring face:	Prism angle 60°/108°
Measuring spindle:	With spindle lock, ø6,35 mm, spindle pitch 0,75 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	5 - 10 N
Setting standard:	167-327 ø 5 mm
Mass:	290 g


Dimensions



a: 0.5 mm



a: 0.5 mm



a: 0.5 mm

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
 Art No. 156-105-10
 Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
 Art No. 156-101-10
Promo price: 55.90 €*
 Suggested retail price: 70.00 €*

Standard accessories:



Setting Standard V-Anvil Micrometer

5mm

Art No. 167-327

Suggested retail price: 66.00 €*
