

## 3 Flute V-Anvil Micrometer

Item number: 114-107

### Images



### Description

This V-Anvil Micrometer helps you measure cutting tools and taps.


It offers the following benefits:

- It measures the outside diameter of cutting tools (such as taps, reamers, end mills) which have three or five flutes.
- V-anvils with a centreline groove are available for measuring the pitch diameter of taps by the single-wire method.


### Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	Including box, spanner, setting standard
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	85 - 100 mm
<b>Graduation:</b>	0,01 mm
<b>Max. Permissible Error J MPE:</b>	$\pm 7 \mu\text{m}$
<b>Anvil:</b>	Without groove
<b>Measuring face:</b>	Prism angle 60°/108°
<b>Measuring spindle:</b>	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,75 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
<b>Measuring force:</b>	5 - 10 N
<b>Setting standard:</b>	167-333 $\varnothing 85$ mm
<b>Mass:</b>	1160 g


### Dimensions



a: 71.1 mm



a: 71.1 mm



a: 71.1 mm

## Accessories

Optional accessories:



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €\***

Suggested retail price: ~~70.00 €\*~~

Standard accessories:



### Setting Standard V-Anvil Micrometer

85mm

Art No. 167-333

Suggested retail price: **352.00 €\***