


Universal Micrometer

Item number: 116-101-10

Images



Description

This Universal Micrometer should be used with optional interchangeable tips. It offers you the following benefits:

- Its non-rotating spindle accepts seven forms of optional interchangeable anvil/spindle tip (including flat, spline, spherical, point, knife-edge, disc, and blade) allowing you to use it in a wide range of applications.
- Optional anvils/spindle-tips for screw thread measurement (matching V and cone) are also available.

Features

Model:	MCN-25B
Digital/Analog:	Analog
Delivered:	Including box, plain and 60° thread setting standard (25 mm- 50 mm), key interchangeable anvils/spindle-tips not included
Inch-Metric:	Metric
Range:	0 - 25 mm
Graduation:	0,01 mm
Spindle feed error:	3 μm
Measuring face:	Interchangeable anvil/spindle inserts (optional)
Measuring spindle:	ø6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	5 - 10 N
Mass:	250 g

Optional accessories:


Measuring Tip

Spherical
Art No. 116-803
Suggested retail price: 71.00 €*



Measuring Tip Point

Art No. 116-804
Suggested retail price: 61.00 €*



Measuring Tip Blade


Art No. 116-807
Suggested retail price: 61.00 €*



Measuring Tip Set for Series 116

7 Pairs (116-801-116-807)
Art No. 116-800
Suggested retail price: 354.00 €*

Measuring Tip Thread Measurement



0,4-0,5mm/64-48TPI
Art No. 116-831
Suggested retail price: 54.00 €*



Measuring Tip Thread Measurement

2-3mm/13-9TPI

Art No. 116-834

Suggested retail price: 54.00 €*

Micrometer Stand, 45° Angle Type



for Micrometer 0-50mm/0-2"

Art No. 156-105-10

Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **55.90 €***

Suggested retail price: 70.00 €*