

Blade Micrometer, Hardened Steel Blade

Item number: 122-102-10

Images



Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	25 - 50 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	$\pm 3 \mu\text{m}$
Delivered:	Including box, spanner, setting standard
Parallelism:	$3 \mu\text{m}$
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type A, hardened steel $t=0.75 \text{ mm}$
Measuring spindle:	$\varnothing 6,35 \text{ mm}$, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
Measuring force:	3 - 8 N
Mass:	300 g

Dimensions



Accessories

Optional accessories:

