

Blade Micrometer, Hardened Steel Blade

Item number: 122-107-10

Images



Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

Digital/Analog:	Analog
Delivered:	Including box, spanner, setting standard
Inch-Metric:	Metric
Range:	150 - 175 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	±5 µm
Parallelism:	5 µm
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type A, hardened steel t=0.75 mm
Measuring spindle:	ø 6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	3 - 8 N
Mass:	950 g

Dimensions



Accessories

Optional accessories:



Micrometer Stand

for Micrometer 100-300mm/5-12"

Art No. 156-102

Suggested retail price: 632.00 €*
*incl. VAT

Standard accessories:



Micrometer Setting Standard

Length: 150mm

Art No. 167-106

Suggested retail price: 43.00 €*
*incl. VAT