


Universal Micrometer

Item number: 116-105-10

Images



Description

This Universal Micrometer should be used with optional interchangeable tips. It offers you the following benefits:

- Its non-rotating spindle accepts seven forms of optional interchangeable anvil/spindle tip (including flat, spline, spherical, point, knife-edge, disc, and blade) allowing you to use it in a wide range of applications.
- Optional anvils/spindle-tips for screw thread measurement (matching V and cone) are also available.

Features

Model:	MCN-1
Digital/Analog:	Analog
Delivered:	Including box, plain and 60° thread setting standard (25 mm- 50 mm), key interchangeable anvils/spindle-tips not included
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0,001"
Spindle feed error:	0.00015 inch
Measuring face:	Interchangeable anvil/spindle inserts (optional)
Measuring spindle:	ø6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	5 - 10 N
Mass:	250 g

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
Art No. 156-105-10
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: **55.90 €*
Suggested retail price: 70.00 €***