

Sheet Metal Micrometer

Item number: 118-116

Images



Description

A non-digital Mitutoyo micrometer provided with a deep frame to enable measurement of sheet metal thickness farther from the edge of a sheet than is possible with a standard micrometer. A ratchet stop guarantees repeatable measurement.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0.0001"
Max. Permissible Error J MPE:	±0.0002"
Delivered:	Including box, spanner
Parallelism:	0.00012"
Measuring face:	Carbide-tipped, micro-lap finish
Anvil / Spindle:	Type B, spherical/flat
Measuring spindle:	With spindle lock, throat depth ≤ 150 mm : ø6,35 mm throat depth =300 mm : ø8 mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	3 - 8 N
Mass:	740 g