

# Blade Micrometer, Hardened Steel Blade

Item number: 122-108-10

## Images



## Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

## Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	175 - 200 mm
<b>Graduation:</b>	0.01 mm
<b>Max. Permissible Error J MPE:</b>	±5 μm
<b>Delivered:</b>	Including box, spanner, setting standard
<b>Parallelism:</b>	5 μm
<b>Measuring face:</b>	Carbide-tipped or hardened steel spindle and anvil
<b>Anvil / Spindle:</b>	Type A, hardened steel t=0.75 mm
<b>Measuring spindle:</b>	ø 6,35 mm, spindle pitch 0.5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, ø18 mm
<b>Measuring force:</b>	3 - 8 N
<b>Mass:</b>	1140 g

## Dimensions



## Accessories

Optional accessories:



## Micrometer Stand

for Micrometer 100-300mm/5-12"

Art No. 156-102

Suggested retail price: 699.00 €\*  
\*including VAT

### Standard accessories:



## Micrometer Setting Standard

Length: 175mm

Art No. 167-107

Suggested retail price: 45.00 €\*  
\*including VAT