

# Blade Micrometer, Hardened Steel Blade

Item number: 122-110-10

## Images



## Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

## Features

<b>Model:</b>	BLM-250B
<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	Including box, spanner, setting standard
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	225 - 250 mm
<b>Graduation:</b>	0.01 mm
<b>Max. Permissible Error J MPE:</b>	±6 μm
<b>Parallelism:</b>	6 μm
<b>Measuring face:</b>	Carbide-tipped or hardened steel spindle and anvil
<b>Anvil / Spindle:</b>	Type A, hardened steel t=0.75 mm
<b>Measuring spindle:</b>	ø 6,35 mm, spindle pitch 0.5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, ø18 mm
<b>Measuring force:</b>	3 - 8 N
<b>Mass:</b>	1450 g


## Dimensions



## Accessories

Optional accessories:

---



**Micrometer Stand**

for Micrometer 100-300mm/5-12"

Art No. 156-102

Suggested retail price: 632.00 €\*  

---

Standard accessories:

---



**Micrometer Setting Standard**

Length: 225mm

Art No. 167-109

Suggested retail price: 58.00 €\*  

---