

Blade Micrometer, Hardened Steel Blade

Item number: 122-115-10

Images



Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features


Model:	BLM-275B
Digital/Analog:	Analog
Delivered:	Including box, spanner, setting standard
Inch-Metric:	Metric
Range:	250 - 275 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	$\pm 6 \mu\text{m}$
Parallelism:	$6 \mu\text{m}$
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type A, hardened steel $t=0.75 \text{ mm}$
Measuring spindle:	$\varnothing 6,35 \text{ mm}$, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
Measuring force:	3 - 8 N
Mass:	1600 g

Dimensions



Accessories

Optional accessories:



Micrometer Stand

for Micrometer 100-300mm/5-12"

Art No. 156-102

Suggested retail price: 632.00 €*

Standard accessories:



Micrometer Setting Standard

Length: 250mm

Art No. 167-110

Suggested retail price: 62.00 €*
