


Blade Micrometer, Hardened Steel Blade

Item number: 122-101-10

Images



Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

| | |
|--------------------------------------|--|
| Digital/Analog: | Analog |
| Delivered: | Including box, spanner |
| Inch-Metric: | Metric |
| Range: | 0 - 25 mm |
| Graduation: | 0.01 mm |
| Max. Permissible Error J MPE: | ±3 μm |
| Parallelism: | 3 μm |
| Measuring face: | Carbide-tipped or hardened steel spindle and anvil |
| Anvil / Spindle: | Type A, hardened steel t=0.75 mm |
| Measuring spindle: | ∅ 6,35 mm, spindle pitch 0.5 mm |
| Scale: | Thimble and sleeve satin chrome finish, ∅18 mm |
| Measuring force: | 3 - 8 N |
| Mass: | 260 g |

Dimensions



Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
Art No. 156-105-10
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: **55.90 €***
Suggested retail price: 70.00 €*
Suggested retail price: 70.00 €*
Suggested retail price: 70.00 €*