

Blade Micrometer, Hardened Steel Blade

Item number: 122-128-10

Images



Description

This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

Model:	BLM-4
Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	3 - 4 "
Graduation:	0.0001"
Max. Permissible Error J MPE:	±0.0002"
Delivered:	Including box, spanner, setting standard
Parallelism:	0.0002"
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type A, hardened steel t=0.75 mm
Measuring spindle:	∅ 6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ∅18 mm
Measuring force:	3 - 8 N
Mass:	550 g

Accessories

Optional accessories:

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Standard accessories:



Micrometer Setting Standard

Length: 3"

Art No. 167-143

Suggested retail price: 37.00 €*