

Blade Micrometer, Carbide-Tipped Blade

Item number: 122-151-10

Images



Description

This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

Model:	BLM-1
Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0.0001"
Max. Permissible Error J MPE:	±0.00015"
Delivered:	Including box, spanner
Parallelism:	0.00015"
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type D, carbide t=0.4 mm
Measuring spindle:	ø 6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	3 - 8 N
Mass:	275 g

Accessories

Optional accessories:

