

# Blade Micrometer, Hardened Steel Blade

Item number: 122-111-10

## Images



## Description


This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	Including box, spanner
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	0 - 25 mm
<b>Graduation:</b>	0.01 mm
<b>Max. Permissible Error J MPE:</b>	$\pm 3 \mu\text{m}$
<b>Parallelism:</b>	$3 \mu\text{m}$
<b>Measuring face:</b>	Carbide-tipped or hardened steel spindle and anvil
<b>Anvil / Spindle:</b>	Type B, hardened steel t=0.4 mm
<b>Measuring spindle:</b>	$\varnothing 6,35 \text{ mm}$ , spindle pitch 0.5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
<b>Measuring force:</b>	3 - 8 N
<b>Mass:</b>	260 g

## Dimensions



## Accessories

Optional accessories:



### Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"  
Art No. 156-105-10  
Suggested retail price: 58.00 €\*  
Suggested retail price: 58.00 €\*  
Suggested retail price: 58.00 €\*

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10  
Promo price: **55.90 €\*  
Suggested retail price: 70.00 €\***