


Blade Micrometer, Hardened Steel Blade

Item number: 122-135-10

Images



Description

This Blade Micrometer is designed to help you measure hard-to-reach features. It offers the following benefits:

- Blade-shaped anvil and spindle for measuring the groove diameter of shafts.
- Non-rotating spindle.

Features

Model:	BLM-1
Digital/Analog:	Analog
Delivered:	Including box, spanner
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0.0001"
Max. Permissible Error J MPE:	±0.00015"
Parallelism:	0.00015"
Measuring face:	Carbide-tipped or hardened steel spindle and anvil
Anvil / Spindle:	Type B, hardened steel t=0.4 mm
Measuring spindle:	∅ 6,35 mm, spindle pitch 0.5 mm
Scale:	Thimble and sleeve satin chrome finish, ∅18 mm
Measuring force:	3 - 8 N
Mass:	260 g

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
Art No. 156-105-10
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: **55.90 €*
Suggested retail price: 70.00 €***