


Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 1231AB-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	With certificate of inspection, bezel clamp
Range:	2.5 mm
Range per rev.:	1 mm
Dial reading:	0-50-0
Graduation:	0,01 mm
MPE first one revolution:	$\pm 10 \mu\text{m}$
MPE first 2 1/2 revolutions:	$\pm 10 \mu\text{m}$
H MPE (Hysteresis):	$3 \mu\text{m}$
R MPE (Repeatability):	$\pm 2 \mu\text{m}$
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

Spindle Lifting Lever

for S-Type and A-Type Serie 1

Art No. 902100

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

Price on application



Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €*
