


Depth Micrometer, Interchangeable Rods

Item number: 129-150

Images



Description

A Mitutoyo non-digital depth micrometer using interchangeable measuring rods to cover a wide measuring range. The base is made from tool steel, hardened and ground with a micro-lapped reference surface.

Features

| | |
|--|--|
| Inch-Metric: | Inch |
| Digital/Analog: | Analog |
| Graduation: | 0,001" |
| Range: | 0 - 12 " |
| Measuring span: | 25 mm |
| Spindle pitch: | 0,5 mm |
| Micrometer Head Feed (0-25 mm): | $\pm 3 \mu\text{m}$ |
| Zero point errors of rods: | $\pm 4 \mu\text{m}$ (0-150 mm) $\pm 6 \mu\text{m}$ (0-300 mm) |
| Parallelism base/rod: | $(4 + L/50) \mu\text{m}$ L=max. measuring length (mm) |
| Measuring face: | Hardened, precision ground, micro-lap finish |
| Base: | Hardened tool steel |

| | |
|------------------------|----|
| Number of rods: | 12 |
|------------------------|----|

| | |
|---------------|--|
| Scale: | Thimble and sleeve satin chrome finish ø18 mm |
|---------------|--|

| | |
|-------------------------|--------|
| Measuring force: | 5-10 N |
|-------------------------|--------|

| | |
|-------------------|----------------|
| Functions: | Base 4 x 0.63" |
|-------------------|----------------|

| | |
|--------------|-------|
| Mass: | 640 g |
|--------------|-------|

| | |
|-------------------|--|
| Delivered: | Including box, spanner no. 301336, 04GAA274, hex-spanner no. 202863 |
|-------------------|--|