


Micrometer Head, Ultra Small Type

Item number: 148-211-10

Images



Description

This ultra-small micrometer head allows you to easily incorporate it into machines and offers you the following benefits:

- Plain stem and a flat spindle end
- Hardened steel measuring surface

Features

| | |
|---|---------------------------|
| Digital/Analog: | Analog |
| Delivered: | With micrometer spanner |
| Inch-Metric: | Metric |
| Range: | 0 - 6.5 mm |
| Graduation: | 0,01 mm |
| Max. Permissible Error J MPE: | ±5 µm |
| Spindle end: | Flat |
| Spindle pitch: | 0,5 mm |
| Stem Ø: | 6 mm |
| Stem: | w/ clamp nut |
| Fixture thickness for clamp nut: | 4 mm |
| Special features: | Reverse reading |
| Measuring face: | Hardened steel (> 60 HRC) |
| Mass: | 10 g |

Dimensions

