

Microm. Head, Spindle Feed

0,25mm/rev.

Item number: 148-323

Images



Description

These micrometer heads are a standard, small-sized type with a 6,5 mm and 13 mm measuring range.


They offer the following benefits:

- Fine spindle feed of 0,25 mm/rev for fine adjustment.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	0 - 6.5 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	±2 μm
Spindle end:	Spherical (SR4)
Spindle pitch:	0,25 mm
Stem Ø:	9.5 mm
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	6 mm
Delivered:	In a paper box with spanner 301336
Measuring face:	Hardened steel (>60 HRC)
Mass:	35 g

Dimensions



Accessories

Optional accessories:



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303559
Suggested retail price: 43.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303568
Suggested retail price: 46.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303563
Suggested retail price: 43.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303572
Suggested retail price: 46.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303561
Suggested retail price: 43.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303570
Suggested retail price: 46.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303565
Suggested retail price: 43.00 €*



Fixture for Micrometer Head, Clamp Nut

for 9,5mm Stem
Art No. 303574
Suggested retail price: 46.00 €*
