

## Micrometer Head, Carbide Tipped Spindle

Item number: 149-185-10

### Images



### Description

This small micrometer head with tungsten carbide measuring surface offers you the following benefits:

- Stem with clamp nut and a flat or spherical spindle end
- Stem with carbide-tipped spindle

### Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0 - 0.5 "
<b>Graduation:</b>	0.001"
<b>Max. Permissible Error J MPE:</b>	±0.0001"
<b>Spindle end:</b>	Flat
<b>Spindle pitch:</b>	0,5 mm
<b>Stem Ø:</b>	375"
<b>Stem:</b>	Plain
<b>Measuring face:</b>	Carbide tipped (>90 HRA)
<b>Mass:</b>	55 g