

Microm. Head, Heavy Duty, 8 mm Spindle

Item number: 151-239

Images



Description

A medium sized, standard, non-digital Mitutoyo micrometer head with M12 clamp-nut stem and heavy-duty ± 8 mm spindle fitted with flat tungsten-carbide tip. Ratchet stop.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 0,1 "
Graduation:	0,001"
Max. Permissible Error J MPE:	± 0.0001 "
Spindle end:	Flat
Spindle pitch:	0,5 mm
Fixture thickness for clamp nut:	25.5 mm
Delivered:	In a paper box with spanner 200154
Measuring face:	Carbide-tipped

Dimensions

