

Micrometer Head Non-rotating Spindle

Item number: 153-203

Images



Description

- Micrometer Head featuring a non-rotating spindle for delicate workpieces
- Design suits applications where the twisting effect of the standard spindle is undesirable because of the risk of damage

Features

Model:	MHK-25
Digital/Analog:	Analog
Delivered:	In a paper box with spanner 301336
Inch-Metric:	Metric
Range:	0 - 25 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	±3 μm
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	12 mm
Stem:	Plain
Measuring face:	Carbide tipped
Mass:	125 g

Dimensions

