

# Groove Micrometer, Non-Rotating Spindle

Item number: 146-234

## Images



## Description

A non-digital tubular Mitutoyo micrometer equipped with concentric, disc-shaped anvils for making measurements inside holes, such as width, depth and location of grooves and projections. Separate graduations for inside and outside measurements avoid need for corrections for anvil thickness. A ratchet stop guarantees repeatable measurement.

## Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range Outside:</b>	2"-3"
<b>Range Inside:</b>	2.05"-3.05"
<b>Graduation:</b>	0,001"
<b>Max. Permissible Error J MPE:</b>	±0.0004"
<b>Delivered:</b>	Including box, spanner
<b>Parallelism:</b>	0.0004"
<b>Measuring face:</b>	Hardened
<b>Measuring spindle:</b>	Spindle pitch 0,5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, ø18 mm
<b>Measuring force:</b>	5 - 10 N
<b>Mass:</b>	165 g

## Dimensions

**L:** 75 mm  
**l:** 65 mm