

Micrometer Head Ultra-small

Item number: 148-204

Images



Description

This ultra-small micrometer head allows you to easily incorporate it into machines and offers you the following benefits:

- Plain stem and a flat spindle end
- Hardened steel measuring surface

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 0.25 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.00025"
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	0.25"
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	4 mm
Delivered:	In a paper box
Measuring face:	Hardened steel (>60 HRC)
Mass:	10 g

Dimensions

