

## Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 1925A-10

### Images



### Description

#### Compact Type, Extra Small Diameter - Inch

This is a compact, inch dial indicator with a bezel  $\varnothing$  31 / 36 mm. It offers you the following benefits:

- It is ideal for use in applications where space is limited.

### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0,025 "
<b>Range per rev.:</b>	0.01 "
<b>Dial reading:</b>	0-5-0
<b>Delivered:</b>	With certificate of inspection
<b>Graduation:</b>	0.0001"
<b>H MPE (Hysteresis):</b>	0,0001"
<b>R MPE (Repeatability):</b>	$\pm$ 0,00003"
<b>MPE first one revolution:</b>	$\pm$ 0,0002"
<b>MPE first 2 1/2 revolutions:</b>	$\pm$ 0,0002"
<b>Type:</b>	ANSI/AGD Standard
<b>Measuring force:</b>	0,3-1,8 N
<b>Stem:</b>	9.52 mm / 0.375"


**Contact point:**

Carbide tipped, thread: 4-48UNF

**Mass:**

56 g

## Dimensions



**A:** 0.61 inch

**B:** 1.48 inch

**C:** 1.22 inch

**D:** 0.52 inch

**E:** 3/4 inch

**F:** 0.59 inch

**G:** 0.28 inch

**H:** 1.18 inch

**I:** 0.27 inch

## Spare parts

Consumable spares:



### Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB056

Suggested retail price: 8.30 €\*