

# Micrometer Head Zero Adjustable

Item number: 148-852

## Images



## Description

A small, standard, zero-adjustable non-digital Mitutoyo micrometer head with M9.5 clamp-nut stem, spherically radiused spindle tip and concentric spindle lock.

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box with hex wrench 202863, spanner 301336
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0 - 0.5 "
<b>Graduation:</b>	0.001"
<b>Max. Permissible Error J MPE:</b>	±0.0001"
<b>Spindle end:</b>	Spherical (SR4)
<b>Spindle pitch:</b>	0,5 mm
<b>Stem Ø:</b>	0.375"
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	6 mm
<b>Measuring face:</b>	Hardened steel (>60 HRC)
<b>Mass:</b>	40 g

## Dimensions

