

Micrometer Head Non-rotating Spindle

Item number: 153-108

Images



Description

- Micrometer Head featuring a non-rotating spindle for delicate workpieces
- Design suits applications where the twisting effect of the standard spindle is undesirable because of the risk of damage

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 0,5 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.00015"
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	0.375"
Stem:	Plain
Delivered:	In a paper box with spanner 200168
Measuring face:	Carbide tipped
Mass:	70 g

Dimensions

