

Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 1670A

Images



Description

Compact Type, Small Diameter - Inch

This is a compact, inch dial indicator with a bezel Ø 40 mm. It offers you the following benefits:


- It is ideal for use in applications where space is limited.
- Green limit markers are a standard accessory.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Delivered:	With certificate of inspection, bezel clamp
Range:	0,1 "
Range per rev.:	0,04"
Dial reading:	0-40
Graduation:	0.0005"
H MPE (Hysteresis):	0,00016"
R MPE (Repeatability):	±0,0001"
MPE first one revolution:	±0,0005"
MPE first 2 1/2 revolutions:	±0,0005"
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N

Mass:	90 g
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes

Dimensions



- A:** 1.28 inch
- B:** 1.71 inch
- C:** 1.57 inch
- D:** 0.59 inch
- E:** 3/4 inch
- F:** 0.5 inch
- G:** 0.42 inch
- H:** 1.5 inch
- I:** 0.26 inch

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator
Art No. 21AAB363
Price on application



Spindle Lifting Lever

for S-Type and A-Type Serie 1
Art No. 902100
Price on application



Spindle Lifting Cable

for Indicator, L=500mm
Art No. 21JZA295
Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €*