


## Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 1671A

### Images



### Description

#### Compact Type, Small Diameter - Inch

This is a compact, inch dial indicator with a bezel Ø 40 mm. It offers you the following benefits:


- It is ideal for use in applications where space is limited.
- Green limit markers are a standard accessory.

### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0,1 "
<b>Range per rev.:</b>	0,04"
<b>Dial reading:</b>	0-20-0
<b>Delivered:</b>	With certificate of inspection, bezel clamp
<b>Graduation:</b>	0.0005"

<b>H MPE (Hysteresis):</b>	0,00016"
<b>R MPE (Repeatability):</b>	±0,0001"
<b>MPE first one revolution:</b>	±0,0005"
<b>MPE first 2 1/2 revolutions:</b>	±0,0005"
<b>Type:</b>	ANSI/AGD Standard
<b>Measuring force:</b>	0,4-1,4 N
<b>Stem:</b>	9.52 mm / 0.375"
<b>Contact point:</b>	Carbide tipped, thread: 4-48UNF
<b>Continuous dial:</b>	Yes
<b>Mass:</b>	90 g

## Dimensions



- A:** 1.28 inch
- B:** 1.71 inch
- C:** 1.57 inch
- D:** 0.59 inch
- E:** 3/4 inch
- F:** 0.5 inch
- G:** 0.42 inch
- H:** 1.5 inch
- I:** 0.26 inch

## Accessories

Optional accessories:



### Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator  
Art No. 21AAB363

**Price on application**



### Spindle Lifting Lever

for S-Type and A-Type Serie 1  
Art No. 902100

**Price on application**

## Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

[Price on application](#)



## Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

[Price on application](#)



### Standard accessories:

## Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

[Price on application](#)



### Spare parts

#### Consumable spares:

## Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €\*



