

Dial Gauge, Flat Back, ISO Type

Item number: 2046AB-60

Images



Description

Standard Type, 10 mm Range, 0.01 mm Graduation

This is a standard dial indicator. It offers you the following benefits:


- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
- No through screw holes on the frame as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Type:	EN ISO Standard
Delivered:	With certificate of inspection
Range:	10 mm
Range per rev.:	1 mm
Dial reading:	± 0.100
Graduation:	0.01 mm
MPE any 1/10 revolution:	5 μ m

MPE any 1/2 revolution:	9 μm
MPE any 1 revolution:	10 μm
MPE measuring range:	13 μm
H MPE (Hysteresis):	3 μm
R MPE (Repeatability):	3 μm
Measuring force:	0,4-2,5 N
Mass:	137 g
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
Continuous dial:	Yes

Dimensions



- A:** 47,2 mm
- B:** 74.7 mm
- C:** 57 mm
- D:** 18.1 mm
- E:** 20 mm
- F:** 12.3 mm
- G:** 33.9 mm
- H:** 52 mm
- I:** 7.6 mm

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application

Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application



Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 14.00 €*



NBR Rubber Boot

Digital Gauge ID-B, Dial Gauge IP63/IP64

Art No. 21AAB562

Suggested retail price: 1.60 €*