


Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 1802A-10

Images



ANSI/AGD Type



Unit: in

Code No.	A	B	C	D	E	F	G	H
1410A	1.26	1.87	1.57	0.59	3/4	0.50	0.58	1.50
1411A	1.26	1.87	1.57	0.59	3/4	0.50	0.58	1.50
1410A-10	1.26	1.87	1.57	0.59	3/4	0.50	0.58	1.50
1780A	1.26	1.74	1.57	0.59	3/4	0.50	0.44	1.50
1781A	1.26	1.74	1.57	0.59	3/4	0.50	0.44	1.50
1560A	1.26	1.74	1.57	0.59	3/4	0.50	0.44	1.50
1561A	1.26	1.74	1.57	0.59	3/4	0.50	0.44	1.50
1670A	1.26	1.71	1.57	0.59	3/4	0.50	0.42	1.50
1671A	1.26	1.71	1.57	0.59	3/4	0.50	0.42	1.50
1802A-10	1.26	1.63	1.57	0.59	3/4	0.50	0.33	1.50
1803A-10	1.26	1.63	1.57	0.59	3/4	0.49	0.33	1.50



Description

Compact Type, Small Diameter - Inch

This is a compact, inch dial indicator with a bezel Ø 40 mm. It offers you the following benefits:


- It is ideal for use in applications where space is limited.
- Green limit markers are a standard accessory.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,025 "
Range per rev.:	0.01 "
Dial reading:	0-10
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0.0001 "

H MPE (Hysteresis):	0,0001"
R MPE (Repeatability):	±0,00003"
MPE first one revolution:	±0,0001"
MPE first 2 1/2 revolutions:	±0,0001"
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes
Shockproof:	Yes
Mass:	95 g

Dimensions



A: 1.28 inch

B: 1.63 inch

C: 1.57 inch

D: 0.59 inch

E: 3/4 inch

F: 0.5 inch

G: 0.33 inch

H: 1.5 inch

I: 0.26 inch

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

Spindle Lifting Lever

for S-Type and A-Type Serie 1

Art No. 902100

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

[Price on application](#)



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

[Price on application](#)



Standard accessories:

Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

[Price on application](#)



Spare parts

Consumable spares:

Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*



